



# GP7 – STATIONARY TOP TABLE SYSTEM

## Choice of 20, 32, 40 or 50 kW High Frequency Generator

### HF Generators


SHF210 – 320 mA, 125 kVp (250 mA @ 80 kVp), 16 mA Stations  
 SHF310 – 400 mA, 125 kVp (400 mA @ 80 kVp), 17 mA Stations  
 SHF410 – 500 mA, 125 kVp (500 mA @ 80 kVp), 18 mA Stations  
 SHF510 – 640 mA, 125 kVp (640 mA @ 78 kVp), 19 mA Stations

- 0.001 to 10 Second Time Range
- 0.1 to 500 mAs
- kVp Selection, 40 to 125 kVp in 1 kV Increments
- Digital Displays
- Automatic Line Compensation
- APR, Anatomical Programming
- Table Mount
- Exposure Hand Switch
- UL/CE/FDA/Listed
- For Operation on 1 Phase 208/240VAC – 3 Phase Optional



### POWER CABINET SPECIFICATIONS

LINE POWERED



### 13-FBT Stationary Top Table

- 76 x 30" (193 x 76 cm) Stationary Top Table
- Table Top Supports Patients up to 300 lbs. (136.1 kg)
- Heavy Duty Grid Cabinet (Bucky Optional) with 103 line, 10:1 Ratio Grid and Cassette Tray

### 13-RA-84 Non-Rotate Tube Stand

- Floor-to-Wall Mounted
- Vertical Travel 9.5" to 78" (24 to 198 cm)
- Fits in Ceiling Heights of 91" to 102" (231 cm to 259 cm)
- Platform Tube Mount, Angulation Dial and Operator Handles
- Magnetic Locks Control Longitudinal, Vertical and Tube Rotation
- 64" (162.5 cm) Longitudinal Travel



### 13-BF-7E Wall Stand with Grid Cabinet

- 84" (213.4 cm) Floor-to-Wall Mounted Column
- Magnetic Locks
- 17 x 17" (43 x 43 cm) Heavy Duty Grid Cabinet with 103 Line, 10:1 Ratio Grid and Cassette Tray
- Bucky, Various Grids and Tilting Mechanism Optional



### E-7239FX X-Ray Tube

- 140,000 Heat Unit
- 1.0 x 2.0 mm Focal Spots
- Other Tubes Optional

### CML125-0001-C

- Manual Collimator
- Laser Light
- Swivel Mount
- LED

### 10539-20 High Voltage Cables

- 20' (609.6 cm) Long

**TXR** • 5481 Skyland Blvd., E • Cottondale, AL 35453

Phone: 205-556-3803 • Fax: 205-556-3824 • 800-897-9729 • www.txr.com • sales@txr.com

Complies with FDA and Product Safety Requirements. • Specifications Subject to Change Without Notice